



G  
Ra1.6

20<sup>0</sup> -0.05

5 ± 0.05

10 ± 0.05

15 ± 0.05

2 ± 0.05

8<sup>0</sup> -0.02

6 ± 0.05

1.5 ± 0.01

3 ± 0.05

5 ± 0.05

0.8

6x φ 0.8 ± 0.02 全貫通

4x C0.1

4x C0.3

DESCRIPTION

ガイドレール

MATERIAL		SURFACE TREATMENT		HEAT TREATMENT		Q'TY
ジルコニア						
SHEET	10:1	DESIGNED	CHECKED	APPROVED		
 3 ANGLE						

2. 指示なき角部の面取りは無し  
1. 指示なき公差は長さ±0.2、角度±0.1°